



**1. Part Numbers:** 5045A-1500

**2. Photograph:**



**3. Product Information:**

Description	Multi Dipper 2 – 1500mm										
Material of Construction:	<table border="0"> <tr> <td>Frame:</td> <td>316L stainless steel</td> </tr> <tr> <td>Chain:</td> <td>316 stainless steel</td> </tr> <tr> <td>Shackles:</td> <td>316 stainless steel</td> </tr> <tr> <td>Bottle Lids:</td> <td>316L stainless steel</td> </tr> <tr> <td>Bottles (8165A-250):</td> <td>HDPE</td> </tr> </table>	Frame:	316L stainless steel	Chain:	316 stainless steel	Shackles:	316 stainless steel	Bottle Lids:	316L stainless steel	Bottles (8165A-250):	HDPE
Frame:	316L stainless steel										
Chain:	316 stainless steel										
Shackles:	316 stainless steel										
Bottle Lids:	316L stainless steel										
Bottles (8165A-250):	HDPE										
Max. Width:	115mm										
Overall Length (sampler & bottles):	1510mm										
No. of Sample Bottles:	3										
Bottle Positions:											



External Finish:	<1 Micron Ra
Nominal Weight:	2.7 Kg (sampler & empty bottles)
Recommended Storage Conditions:	Dry and ambient temperature

**4. Approval:**

Signed:



Name: Kuldeep Flora  
Position: Quality Manager  
Date: 21-Jan-25